



APPROVED 4S. 'STICK' Lithium (LiPo) BATTERY LIST. 2018. v1.

List shows years :- 2017 -- 2018.

Only Batteries detailed below (and any archive lists) are approved for EFRA Sanctioned Events.

EUROPEAN FEDERATION RADIO CONTROLLED AUTOMOBILES.

BATTERIES ON THIS HOMOLOGATION LIST HAVE BEEN CERTIFIED FOR COMPLIANCE WITH UN38.3, TESTS T1-T8.

Lithium based (LiPo) batteries detailed below, are approved for various EFRA Electric Classes. Section Rules will detail the type applicable. Availability dates for new EFRA compliant Packs are not known at the date of publishing this list. Manufacturers have confirmed March 2018 latest.

EFRA rules do not limit battery power output, but energy capacity has to comply with Airline Requirements, based on Manufacturers data below.

Batteries approved from 2011 onwards must comply with the weight range specified. Batteries factory sealed (glue, weld etc.).




Battery packs must be able to be disconnected within the Car quickly without the use of tools. Direct soldering is not allowed.

Manufacturers advise that charge rate be restricted to 1C for optimum lifespan, but should not be more than stated below (for 2017 on).

Batteries MUST be charged using a 4S LiPo compatible charger. LiPo 'Sack' must be used when charging or discharging prior to race.



It is strictly NOT ALLOWED, to charge 4S LiPo Batteries to give an output voltage exceeding 16.80v.

Submitted by:	Label Details Part #	Illustration only	Manufacturer Supplied Data.	EFRA measured Specification,	Approval Date
BATTERIES BELOW ARE APPROVED BY EFRA FOR 2018, BUT NOT ALLOWED AT 2018 EVENTS UNTIL 01.04.18.					
Associated Electrics	Reedy Zappers # 27328		Reedy LiPo 4S 15.2v. 98.0 Wh. 110C Max charge rate: 3C 5 mm. Tubes	Sample complies with BRCA dimensions. Weights:- Sample: 548.7 g. Allowed: 528/572 g.	18.01.18
Intellect Battery	IP # CC4S5200HV3		Intellect LiPo 4S 15.2v. 79.0 Wh. 120C Max charge rate: 3C 5 mm. Tubes	Sample complies with BRCA dimensions. Weights:- Sample: 469.2 g. Allowed: 446/484 g.	18.01.18
Intellect Battery	IP # CC4S6000HV3		Intellect LiPo 4S 15.2v. 91.0 Wh. 120C Max charge rate: 3C 5 mm. Tubes	Sample complies with BRCA dimensions. Weights:- Sample: 533.8 g. Allowed: 509/551 g.	18.01.18
LRP	LRP P5 Offroad # 430269		LRP LiPo 4S 14.8v. 97.7 Wh. 120C Max charge rate: 3C 5 mm. Tubes	Sample complies with BRCA dimensions. Weights:- Sample: 622.2 g. Allowed: 599/649 g.	18.01.18
Neidhart SA	Orion Ultimate # ORI 14516		Orion LiPo 4S 14.8v. 97.7 Wh. 120C Max charge rate: 3C 5 mm. Tubes	Sample complies with BRCA dimensions. Weights:- Sample: 578.6 g. Allowed: 553/600 g.	18.01.18
Nosram	Nosram P5 Offroad # 999551		Nosram LiPo 4S 14.8v. 97.7 Wh. 120C Max charge rate: 3C 5 mm. Tubes	Sample complies with BRCA dimensions. Weights:- Sample: 626.0 g. Allowed: 599/649 g.	18.01.18
Shenzhen Grepow	GensAce # B100C67504S1 P HC-50-HV-RS		GensAce LiPo 4S 14.8v. 99.9 Wh. 100C Max charge rate: 1C 5 mm. Tubes	Sample complies with BRCA dimensions. Weights:- Sample: 586.1 g. Allowed: 563/609 g.	18.01.18
Team Corally	Corally Voltax # C-49530		Corally LiPo 4S 14.8v. 96.2 Wh. 120C Max charge rate: 2C 5 mm. Tubes	Sample complies with BRCA dimensions. Weights:- Sample: w/w 570.9 g. Allowed: 549/595 g.	18.01.18

Team Corally	Corally Voltax # C-49631		Corally LiPo 4S 15.2v. 99.0 Wh. 120C Max charge rate: 2C Wires	Sample complies with BRCA dimensions. Weights:- Sample: w/w 609.0 g. Allowed: 584/635 g.	18.01.18
Team Corally	Corally Voltax # C-49630		Corally LiPo 4S 15.2v. 99.0 Wh. 120C Max charge rate: 2C 5 mm. Tubes	Sample complies with BRCA dimensions. Weights:- Sample: w/w 551.6 g. Allowed: 530/574 g.	18.01.18
Team Corally	Corally Voltax # 49531		Corally LiPo 4S 14.8v. 99.9 Wh. 120C Max charge rate: 2C Wires	Sample complies with BRCA dimensions. Weights:- Sample: w/w 604.3 g. Allowed: 580/628 g.	18.01.18

BATTERIES BELOW THIS LEVEL WERE APPROVED BY EFRA FOR 2017 AND ARE ALLOWED AT ALL 2018 EVENTS.

Intellect Battery	IP # CC4S6000HV2		Intellect LiPo 4S 15.2v. 91.0 Wh. 120C Max charge rate: 3C 5 mm. Tubes	Sample complies with EFRA dimensions. Weights:- Sample: 543.8 g. Allowed: 528/572 g.	05.01.17
LRP	LRP # 430246		LRP LiPo 4S 14.8v. 97.7 Wh. 110C Max charge rate: 3C 5 mm. Tubes	Sample complies with EFRA dimensions. Weights:- Sample: 637.3 g. Allowed: 609/659 g.	05.01.17
Modern Creations	Team Silverback Spiral R # 6750904SIN		Modern Creations LiPo 4S 14.8v. 99.9 Wh. 90C Max charge rate: 3C 5 mm. Tubes	Sample complies with EFRA dimensions. Weights:- Sample: 530.5 g. Allowed: 509/551 g.	05.01.17
Muchmore Racing	Impact # MLI-4SLCG5200FD2		Muchmore LiPo 4S 14.8v. 76.9 Wh. 110C Max charge rate: 1C Wires	Sample complies with EFRA dimensions. Weights:- Sample: w/w 453.7 g. Allowed: 434/470 g.	05.01.17
Neidhart SA	Orion # ORI 14084		Orion LiPo 4S 14.8v. 71.0 Wh. 110C Max charge rate: 3C 5 mm. Tubes	Sample complies with EFRA dimensions. Weights:- Sample: 436.5 g. Allowed: 418/452 g.	05.01.17
Neidhart SA	Orion # ORI 14090		Orion LiPo 4S 14.8v. 71.0 Wh. 110C Max charge rate: 3C Wires	Sample complies with EFRA dimensions. Weights:- Sample: w/w 469.6 g. Allowed: 451/489 g.	05.01.17
Nosram	Nosram X-treme Race # 999539		Nosram LiPo 4S 14.8v. 97.7 Wh. 110C Max charge rate: 3C 5 mm. Tubes	Sample complies with EFRA dimensions. Weights:- Sample: 638.5 g. Allowed: 609/659 g.	05.01.17
ProTek RC	ProTek RC # PTK-5106-17		ProTek LiPo 4S 15.2v. 98.8 Wh. 100C Max charge rate: 3C 5 mm. Tubes	Sample complies with EFRA dimensions. Weights:- Sample: 540.5 g. Allowed: 528/572 g.	05.01.17

Team Corally	Corally Coral-X # 48375		Corally LiPo 4S 15.2v. 98.8 Wh. 100C Max charge rate:1.3C Wires	Sample complies with EFRA dimensions. Weights:- Sample: w/w 573.4 g. Allowed: 551/597 g.	05.01.17
Team Corally	Corally X-Treme # 48242		Corally LiPo 4S 14.8v. 98.8 Wh. 90C Max charge rate:1.3C Wires	Sample complies with EFRA dimensions. Weights:- Sample: w/w 495.7 g. Allowed: 475/515 g.	05.01.17
Paul Worsley, (EFRA Battery Homologation Officer). Updated - 18.01.18. (Three Pages).					